

BALANCE PROMOTION

ALL LA-SERIES AND LT-SERIES

BALANCES ON SALE UNTIL 9-30-2021!



	Semi Micro		Analytical	
Model	LA-225.C2	LA-164.C2	LA-224.C2	LA-314.C2
Maximum Capacity	82/220 g	160 g	220 g	310 g
Readability [d]	0.01/0.1 mg	0.1 mg	0.1 mg	0.1 mg
Repeatability	0.015 mg	0.1 mg	0.1 mg	0.1 mg
Linearity	±0.05/0.2 mg	±0.2 mg	±0.2 mg	±0.2 mg
Adjustment	Internal			
Stabilization Time	2 sec	2 sec	2 sec	2.5 sec
Pan Size	9.0 cm (3.5")	10.0 cm (4")		
Unit Dimensions	33.3 x 20.6 x 28 cm (13.1 x 8.1 x 11")			
Communication ports	2 x RS232, USB (A&B), Ethernet, Wireless Connection			
List Price	\$4,295.00	\$2,395.00	\$2,695.00	\$2,846.00
Sale Price	\$3,779.60	\$2,107.60	\$2,371.60	\$2,504.48
Catalog Number	10102-23	10102-24	10102-25	10102-26

	Milligram		Toploader		
Model	LT-363.C	LT-603.C	LT-2102.C	LT-4502.C	LT-6002.C
Maximum Capacity	360 g	600 g	2100 g	4500 g	4500 g
Readability [d]	1 mg	1 mg	0.01 g	0.01 g	0.01 g
Repeatability	1 mg	1 mg	0.01 g	0.01 g	0.01 g
Linearity	±2 mg	±3 mg	±0.02 g	±0.02 g	±0.02 g
Adjustment	Internal				
Stabilization Time	2 sec		1.5 sec		
Pan Size	12.8 x 12.8 cm (5 x 5")		19.5 x 19.5 cm (7.7 x 7.7")		
Unit Dimensions	33.5 x 20.6 x 34.8 cm (13.8 x 8.1 x 13.7")				
Communication ports	2 x RS232, USB (A&B), Ethernet, Wireless Connection				
List Price	\$1,595	\$1,795	\$1,595	\$1,795	\$1,995
Sale Price	\$1,460.80	\$1,628.00	\$1,443.20	\$1,614.80	\$1,795.20
Catalog Number	10102-27	10102-28	10102-30	10102-31	10102-32